

nVent CADDY Pyramid Universal Support



FEATURES

Captive stainless steel nuts allow for custom attachment methods to the support base including easy attachment of stainless steel strut, threaded rod or other project-specific hardware

Foam bottom offers low abrasion interface for better roof membrane protection

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Multiple sizes and load ratings offer the ability to tailor the solution to the application

Includes square holes for creating an H-Frame with a 12" (305 mm) cross support (PBU16 only)

Base is manufactured from UV-stabilized thermoplastic material

SPECIFICATIONS

Static Load Safety Factor: 3:1

Material: Polyethylene;Polypropylene;Stainless Steel 18-8 (EN 1.4305)

Temperature: -45 to 65 °C


Table 1/2

Catalog Number	Article Number	Length 1 (L1)	Length 2 (L2)	Height (H)	Width (W)	Thread Size (TS)
PBU6	360488	139.7 mm	203 mm	101.6 mm	152 mm	3/8" UNC
PBU10	360489	254 mm	317.5 mm	101.6 mm	203 mm	3/8" UNC
PBU16	360490	406 mm	483 mm	101.6 mm	203 mm	3/8" UNC

Table 2/2

Catalog Number	Article Number	Hole Quantity	A	B	Surface Area	Static Load
PBU6	360488	3	114.3 mm	57.2 mm	26452mm ²	1330N
PBU10	360489	2	218.4 mm		59355mm ²	4450N
PBU16	360490	2	165.1 mm		91613mm ²	6670N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

