


# Intermediate Adapter to Assemble Several 3 U Testadapter



Bracket kit to make a 6 / 9 U Testadapter from 3 U Testadapters. Suitable for Testadapters with DIN 41612 connectors Type B, C, E and F.

## CERTIFICATIONS



## FEATURES

Suitable for types B, C, D, E, F

## SPECIFICATIONS

Table 1/1

| Catalog Number | Works With    | Material | Package Quantity | Finish        | Quick Ship |
|----------------|---------------|----------|------------------|---------------|------------|
| 20800-224      | Test Adapters | Steel    | 2                | Powder Coated | No         |
| 20800-168      | Test Adapters | Steel    | 2                | Powder Coated | No         |
| 20800-278      | Test Adapters | Steel    | 2                | Powder Coated | No         |

| Catalog Number | Works With    | Material | Package Quantity | Finish        | Quick Ship |
|----------------|---------------|----------|------------------|---------------|------------|
| 20800-279      | Test Adapters | Steel    | 2                | Powder Coated | No         |
| 23040-001      | Test Adapters | Steel    | 2                | Powder Coated | No         |

## ADDITIONAL PRODUCT DETAILS

Test adaptor for DIN connector type D cannot be combined with other types.

Test adaptor depth (dimension B) of VMEbus test adaptors on corresponding product page.

Test adaptor depth (dimension B) of type B, C, D, E, F test adaptors on corresponding product page.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**