

# Non-Insulated Rail Signal Bondstrand



## FEATURES

Highly flexible and resistant to vibration fatigue

Allows mechanical or compressed types of connections as well as nVent ERICO Cadweld welded connections

Meets or exceeds recommendations and design criteria described in AREMA® Manual Parts 8.1.20, 8.1.25, 8.1.30, 8.1.32 and 10.3.12

## SPECIFICATIONS

**Number of Wires:** 133  
**Material:** Copper Magnesium

Table 1/1

Catalog Number	Conductor Type	Conductor Size	Length
SBS8CBARE	AREMA® S-8	3/16" Bondstrand	30.4m
SBS8LBARE	AREMA® S-8	3/16" Bondstrand	152.4m
SBS8BARE	AREMA® S-8	3/16" Bondstrand	304.8m
SBS17CBARE	AREMA® S-17	5/16" Bondstrand	30.4m

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including cadmium, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**