

Hydraulic Pump and Foot Controller



CERTIFICATIONS



FEATURES

Directly connects to a single hydraulic tool for operation or can be used as a spare for the Hydraulic nVent ERIFLEX Flexibar and Busbar Work Center

Pump includes hose with quick-release coupler

Foot controller includes two pedals with off, on and safety off positions

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Voltage	Power	Operating Pressure	Oil Flow	Tank Capacity
HYDR-PMP-230V	545700	230 V	370W	700bar	0.2l/min	1.900 - 3.8 l

Table 2/2

Catalog Number	Article Number	Unit Weight
HYDR-PMP-230V	545700	40 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE