

Cover Cap, WO60



The cover cap cover terminals or connections sets for touch protection.

INDUSTRY STANDARDS

UL

CSA

GL

FEATURES

Description: Cover cap, 3-pole. May also be used as a reserve section cover.

Approvals: CSA, UL, GL, DNV-GL

SPECIFICATIONS

Table 1/1						
Catalog Number	Height	Width	Depth	Material	Finish	Color
01590	54mm	200mm	55mm	Plastic	Textured	Light Gray
01413	84mm	200mm	55mm	Plastic	Textured	Light Gray
01540	250mm	200mm	90mm	Plastic	Textured	Light Gray
01756	135mm	200mm	90mm	Plastic	Textured	Light Gray
01596	228mm	200mm	90mm	Plastic	Textured	Light Gray
01539	180mm	200mm	90mm	Plastic	Textured	Light Gray

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE