

EDT2 DIN Rail Surge Protection Replacement Module



CERTIFICATIONS



SPECIFICATIONS

Catalog Number	EDT2150M	EDT2300M	EDT2350M	EDT2480M	EDT275M
Nominal System Voltage (Un)	120 V	240 V	277 V	400 V	60 V
Max Continuous Operating Voltage (Uc)	150 V	300 V	350 V	480 V	75 V
Nominal Discharge Current (In), IEC	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s
Max Discharge Current (Imax), IEC	50kA 8/20 μ s	50kA 8/20 μ s	50kA 8/20 μ s	50kA 8/20 μ s	50kA 8/20 μ s
Nominal Discharge Current (In), UL	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s
Frequency	50 - 60 Hz	50 - 60 Hz	50 - 60 Hz	50 - 60 Hz	50 - 60 Hz
Temperature	-35 to 85 °C	-35 to 85 °C	-35 to 85 °C	-35 to 85 °C	-35 to 85 °C

Catalog Number	EDT2150M	EDT2300M	EDT2350M	EDT2480M	EDT275M
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Certifications	UR, CE, ERICO EDT2, VDE, cUR	cUR, UR, CE, ERICO DT2 Series, VDE	UR, VDE, cUR, CE, ERICO DT2 Series	VDE, CE, ERICO DT2 Series	CE, ERICO EDT2, VDE

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE