


Collar Screw, Knurled Head Short Version



CERTIFICATIONS



FEATURES

Collar Screw, Knurled Head Short Version

SPECIFICATIONS

Works With: Front Panels

Type: Screw

Product Type: Screw

Table 1/2

Catalog Number	Length	Material	Finish	Package Quantity	Thread Size	Depth
21101-749	12.3mm	Brass	Nickel Plated	100	M2.5	18.3mm
21101-106	11mm	Steel			M2.5	
21100-268	11mm	Brass	Nickel Plated	100	M2.5	

Table 2/2

Catalog Number	Height	Width	Torque	Certifications	Quick Ship
21101-749	8mm	8mm	0.3N·m	RoHS	No
21101-106					No
21100-268					No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE