


Insertor/Extractor Handle Type IET, Grey Lever, Black Button, Bottom, 100 Pieces

CATALOG NUMBER

20817-715



The inserter/extractor handle, type IET in accordance with IEEE 1101.10. 0,1" offset. Two of these handles can overcome a single lever force of 700 N (per pair).

CERTIFICATIONS



Suitable for insertion and extraction forces up to 700 N (per pair)
In accordance with IEEE 1101.10 and IEC 60297-3-102
A microswitch can be mounted
0.1" offset is used for PSUs with SMD Plus

Package Quantity: 100
Handle Type: IET; Bottom Front
Flammability Rating: UL® 94V-0
Color: Grey
Material: Polycarbonate
Product Type: Handle
Type: Inserter/Extractor, 0.1" Offset
Works With: Front Panels
Gross Weight: 2.321kg

Please order Coding pegs and Microswitch separately.

[illegible]

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE