

# NM Cable to Rod/Wire Clip



## CERTIFICATIONS



## FEATURES

Supports non-metallic sheathed cable with ground wire

Increased capability and application options by combining 4Z and 6Z products into one enhanced and efficient offering

Improved multi-function clip allows for optimized inventory while reducing job site scheduling risks associated with multiple SKUs

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material     | Finish             | Flange Thickness | Outer Diameter | Rod Size    |
|----------------|----------------|--------------|--------------------|------------------|----------------|-------------|
| RMX4Z34        | 171096         | Spring Steel | nVent CADDY Armour | 3.9 - 9.5 mm     | 7 - 8 mm       | 4, 6, 8, 10 |

Table 2/2

| Catalog Number | Article Number | Wire Size    |
|----------------|----------------|--------------|
| RMX4Z34        | 171096         | 3.9 - 4.8 mm |

ADDITIONAL PRODUCT DETAILS

Assemblies allow support from most main and substructures.

4Z parts installed on 3/8" (M10) smooth rod in the F2 direction has a Static Load Rating of 15 lb (67 N).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

