

S Hook




FEATURES

For suspending chains, perforated bands, and similar items

SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Material	Finish	Diameter (Ø)	Length (L)	Static Load
S30EG	591570	Steel	Electrogalvanized	3 mm	25mm	120N
S40S4	591650	Stainless Steel 304 (EN 1.4301)		4 mm	35mm	250N
S40EGSP25	172420	Steel	Electrogalvanized	4 mm	35mm	250N
S40EG	591580	Steel	Electrogalvanized	4 mm	35mm	250N
S50EG	591590	Steel	Electrogalvanized	5 mm	45mm	400N
S50S4	591660	Stainless Steel 304 (EN 1.4301)		5 mm	45mm	400N



nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Germany:
800 1890272
Other Countries:
+31 13 5835404

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

