

# Crimping Compression Tool, Hydraulic, Heavy Duty

## Data Solutions



### FEATURES

Wide cross section range

Applies a high level of force

Ergonomic design

Lightweight and easy to use

Includes easy-to-carry custom case

### SPECIFICATIONS

Table 1/1

| Catalog Number | Article Number | Applied Force | System         | Dies                     | Crimping Shape | Conductor Size                                                                                  |
|----------------|----------------|---------------|----------------|--------------------------|----------------|-------------------------------------------------------------------------------------------------|
| M3H            | 716550         | 130kN         | Hand hydraulic | RKM3 series, PKM3 series | Hexagon        | #6 Stranded - 800 kcmil<br>Stranded, 16 mm <sup>2</sup> Stranded - 400 mm <sup>2</sup> Stranded |

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**