

# Special Track Work Complete Welder, Signal

## Data Solutions



### FEATURES

Molds designed for conductor connections to frog and special track work applications

For use on non-load-bearing rail

Includes mold cleaner and flint ignitor

### SPECIFICATIONS

**Material:** Graphite; Steel

**Rail Type:** Manganese Frog

Table 1/1

Catalog Number	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Handle Length
SBTBTB4B	3/4" Tab	3/16" Bondstrand	4.76mm	TB4	381mm
SBTBTB4C	1" Tab	3/16" Bondstrand	4.76mm	TB4	381mm
SBTBTB4CL	1" Tab	3/16" Bondstrand	4.76mm	TB4	584.2mm
SBXSTB4A	1" Tab	3/16" Bondstrand	4.76mm	TB4	381mm

Catalog Number	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Handle Length
SBTBTB4E	1" Tab	5/16" Bondstrand	7.94mm	TB4	381mm

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE