

QCC nVent ERIFLEX Flexibar Clamp



CERTIFICATIONS



FEATURES

Connects nVent ERIFLEX Flexibar to punched busbar

Allows for excellent electrical contact

Compact, space saving design

Installs quickly and easily

Ideal for on site modifications

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel


Table 1/2									
Catalog Number	Article Number	Conductor Width	Depth (D)	Height (H)	Width (W)	Thickness (T)			
QCC15-5-32	561210	15.5 - 32 mm	13mm	35 mm	70 mm	5 mm			
QCC40-63	561220	40 - 63 mm	13mm	35 mm	95 mm	5 mm			

Table 2/2									
Catalog Number	Article Number	A	В	С	Unit Weight				
QCC15-5-32	561210	50 mm	10.5 mm	11 mm	0.11 kg				
QCC40-63	561220	75 mm	10.5 mm	11 mm	0.16 kg				

ADDITIONAL PRODUCT DETAILS

Use one clamp when nVent ERIFLEX Flexibar thickness is less than 5 mm (0.2") and two clamps when nVent ERIFLEX Flexibar thickness is greater than 5 mm (0.2").

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE