

Varistar CP Glazed Door With 3-Point Locking, RAL 7021, 38 U, 1800 H, 800W

Power Utilities

CATALOG NUMBER

21630-423



Glass door with 3 point locking allows stronger adhesion between door and the cabinet frame. This prevents the metal mealeability to show and provides the door extra robustness.

FEATURES

Glazed Door With 3-Point Locking, With Lock

Lever handle with key insert (2 keys)

Opening angle 180°

Security glass, 6 mm

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

PRODUCT ATTRIBUTES

Product Type: Cabinet Door

Product Family: Varistar CP

Type: Glass Door

Works With: Varistar CP

Locking Type: 3-Point Locking

Color: Black Grey

Color Code: RAL 7021

Rack Height: 38 U

Height: 1800 mm

Width: 800 mm

Protection Rating: IP20

Complies With: IEC 61587-1; IEC 61587-3

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE