


# Outdoor Unibody VENT Cabinet

## Power Utilities



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity.

## CERTIFICATIONS



## FEATURES

Double-walled, Al

Forced heat dissipation via fan assembled in side panel, max. 35 W/K

IP 55

One-piece inner case with removable outer cladding

## SPECIFICATIONS

Table 1/2

| Catalog Number | Product Type    | Product Family | Rack Height | Height  | Width  | Depth  |
|----------------|-----------------|----------------|-------------|---------|--------|--------|
| 11249-007      | Outdoor Cabinet | Unibody        | 16 U        | 930 mm  | 700 mm | 500 mm |
| 11249-009      | Outdoor Cabinet | Unibody        | 20 U        | 1100 mm | 700 mm | 500 mm |

| CatalogNumber | Product Type    | Product Family | Rack Height | Height  | Width  | Depth  |
|---------------|-----------------|----------------|-------------|---------|--------|--------|
| 11249-012     | Outdoor Cabinet | Unibody        | 25 U        | 1330 mm | 700 mm | 500 mm |

Table 2/2

| Catalog Number | Wall Type     | Door Type   | Access | Cooling         | EMC Shielding | Complies With                                                                                                          |
|----------------|---------------|-------------|--------|-----------------|---------------|------------------------------------------------------------------------------------------------------------------------|
| 11249-007      | Double Walled | Single Door | Front  | Fan Ventilation | No            | IEC 61969-1,<br>IEC 61969-2,<br>IEC 60917-1,<br>IEC 60917-2,<br>ETS 300119,<br>IEC 60529, DIN<br>EN 50178, VDE<br>0160 |
| 11249-009      | Double Walled | Single Door | Front  | Fan Ventilation | No            | IEC 61969-1,<br>IEC 61969-2,<br>IEC 60917-1,<br>IEC 60917-2,<br>ETS 300119,<br>IEC 60529, DIN<br>EN 50178, VDE<br>0160 |
| 11249-012      | Double Walled | Single Door | Front  | Fan Ventilation | No            | IEC 61969-1,<br>IEC 61969-2,<br>IEC 60917-1,<br>IEC 60917-2,<br>ETS 300119,<br>IEC 60529, DIN<br>EN 50178, VDE<br>0160 |

## ADDITIONAL PRODUCT DETAILS

Please order wall-mounting assembly kit separately.

Further base/plinth heights on request.

Please order panel/slide mounts separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**