


EuropacPRO Rear Angle for Textile EMC Gasket



EuropacPro rear angle for Textile EMC Gasket, out of Aluminum extrusion with etched surface. Rear hood cannot be mounted simultaneously.

CERTIFICATIONS



FEATURES

Required for rear shielding

Also useable at the front if you use a depth-adjustable 19" support bracket

SPECIFICATIONS

Material:	Aluminum
Product Type:	Cover
Product Family:	EuropacPRO
Type:	Rear Angle
Works With:	Subracks

Table 1/1

Catalog Number	Rack Height	Package Quantity	Height	Package Unit	Quick Ship
24564-199	3U	2	132.6mm	Pair	No
24564-799	9U	2	399.3mm	Pair	No
24564-299	4U	2	177mm	Pair	No

Catalog Number	Rack Height	Package Quantity	Height	Package Unit	Quick Ship
24564-499	6U	2	265.9mm	Pair	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE