

Concept Panels

Data Solutions



Concept panels are taller and wider than corresponding NEMA-size panels.

FEATURES

Painted white or conductive finish

Include a formed flange along any side that is longer than 22.20 in (564 mm)

Optional wood panels are made of 3/4-in plywood, pre-cut and pre-drilled to install on panel mounting studs in the rear of the cabinet

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Height	Width	Material	Finish	Color
CP2020W	23785	462mm	462mm	Plywood	Smooth Matte	
CP3220W	23786	767mm	462mm	Plywood	Smooth Matte	
CP4420W	23787	1072mm	462mm	Plywood	Smooth Matte	
CP3220	23782	767mm	462mm	Mild Steel	Powder Coated	White
CP4420	23783	1072mm	462mm	Mild Steel	Powder Coated	White

CatalogNumber	Article Number	Height	Width	Material	Finish	Color
CP5620	23784	1351mm	462mm	Mild Steel	Powder Coated	White

Table 2/2

Catalog Number	Article Number	Thickness	Type
CP2020W	23785	19mm	Wood
CP3220W	23786	19mm	Wood
CP4420W	23787	19mm	Wood
CP3220	23782	2.66mm	Painted Steel
CP4420	23783	2.66mm	Painted Steel
CP5620	23784	2.66mm	Painted Steel

ADDITIONAL PRODUCT DETAILS

Catalog number CP4230 is used on Concept disconnect enclosures.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE