

Door Contact Switch Without Cable

Data Solutions

Door contact switch with magnetic contact, allows operational efficiency. This product is easy handlable by plug and play.



CERTIFICATIONS



FEATURES

Door contact switch (without connection cable)

SPECIFICATIONS

Table 1/2

Catalog Number	Depth	Height	Operating Temperature	Protection Rating	Width	Complies With
20118-810	33.5mm	76.5mm	-25 to 75°C	IP66	31mm	UL® 508, EN 50047 form B

Table 2/2

Catalog Number	Current Rating	Package Quantity	Voltage	Wire Size
20118-810	3 – 6A	1	24 – 230V	0.5 – 2.5mm ²

ADDITIONAL PRODUCT DETAILS

Please order bracket for installation of door switch (Varistar, Novastar, Eurorack) separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE