

# **Industrial Stack Bonding Lug**



## **CERTIFICATIONS**





#### **FEATURES**

Cast lug for bonding conductors to structural features

## **SPECIFICATIONS**

Conductor Size, UL: Class 1 - Class 2 (4/0 Max)


Table 1/2							
Catalog Number	Material	Finish	Hole Size (HS)	Contact Area	Depth (D)	Height (H)	
LPS451	Stainless Steel 316L (EN 1.4404)		19.05 mm	19 cm² Min	27mm	104.78 mm	
LPC451	Brass		19.05 mm	19 cm² Min	27mm	104.78 mm	
LPLC451	Brass	Lead Covered	19.05 mm	19 cm² Min	27mm	104.78 mm	


Table 2/2						
Catalog Number	Width (W)	Unit Weight	Certifications			
LPS451	54 mm	0.28 kg	E202878-Combined_CoC, E202878-Combined_CoC			
LPC451	54 mm	0.33 kg	E202878-Combined_CoC, E202878-Combined_CoC			
LPLC451	54 mm	0.68 kg				

#### ADDITIONAL PRODUCT DETAILS

Where applicable, lead covering thickness is a minimum of 1/16" (1.59 mm) and is not included in the stated dimensions.

#### **DIAGRAMS**





#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

MARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE