

# **Vise Clamp for Telecom**



## **FEATURES**


Used to bond messenger wire to ground tap conductors


When clamp is tightened, the piercing teeth puncture the insulation on the messenger wire, forming a positive ground connection without stripping the cable


## **SPECIFICATIONS**

Table 1/2							
Catalog Number	Material	Finish	Height (H)	Width (W)	Depth (D)	Diameter (Ø)	
EVC167P	Copper Alloy, Stainless Steel 304 (EN 1.4301)	Tinned	41.3 mm	31.8 mm	25.4mm	3.7 - 7.93 mm	

Table 2/2					
Catalog Number	Thread Size (TS)	Unit Weight			
EVC167P	5/16" UNC	0.1 kg			







### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

# Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

# **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY HOFFMAN TRACHTE ERICO ILSCO SCHROFF**