

Elbow 22.50-Degree Feed-Through



Feed-Through 22.50-Degree Elbows are used for continuous runs with 22.50-degree turns. Connects to other wireway sections and fittings and protects wires and cables against dust in a broad range of industrial applications.

INDUSTRY STANDARDS

Certified by Canadian Standards Association.

FEATURES

Feed-Through 22.50-Degree Elbows are used for continuous runs with 22.50-degree turns

Connects to other wireway sections and fittings and protects wires and cables against dust in a broad range of industrial applications

SPECIFICATIONS

- Color Code:

ANSI 61
- Color:

Gray
- Material:

Mild Steel
- Finish:

Powder Coated

Table 1/1						
Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
F22WE225	15740	Elbow	64mm	64mm	1.9mm	No
F88WE225	15770	Elbow	203mm	203mm	1.9mm	No
F66WE225	15760	Elbow	152mm	152mm	1.9mm	No
F44WE225	15750	Elbow	102mm	102mm	1.9mm	No

ADDITIONAL PRODUCT DETAILS

All dimensions are to outside surfaces. Allow .12 in. (3 mm) additional for gasket at joints.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE