

# HN 3R Side-Mount Filter Fans Reverse 115V, 5.91x5.91x2.92, Black, Plastic

## CATALOG NUMBER

**HN0516513R**



HN 3R Side-Mount Filter Fans quickly install into enclosure with a click-fit design; no tools or screws required. Grilles open with the flick of a finger for easy filter replacement.

## INDUSTRY STANDARDS

UL/cUL Listed; File No. E482010

CE, UK CA, UL

Type 12, 3R standard

IP55 standard on all models except HN04

## FEATURES

Click-fit design quickly installs into enclosure wall; no tools or screws required

Grille opens with the flick of a finger for easy filter replacement

Enclosure side wall mounting

Reverse airflow option on items ending with "R" available to push/pull air through higher static pressure

Standard rope gasket provides proper seal to the enclosure

Similar cut-out sizes as other filter fan manufacturers

Terminal block connections

Optional thermostat available to save energy and extend service life

Hinged grille remains attached after opening

Size range from 4 in. (102 mm) to 12 in. (305 mm)

Service life hours from 40,000 to 98,000 hours

## PRODUCT ATTRIBUTES

Article Number: 59934

Airflow: 56m<sup>3</sup>/h

Nominal Voltage: 115V

Height: 150mm

Width: 150mm

Depth: 74mm

Max Current: 0.26A

Operating Temperature: -10 to 55°C

Material: Plastic

Finish: Smooth Matte

Color: Black

Color Code: RAL 9005

## ADDITIONAL PRODUCT DETAILS

---

Unit depth is of the entire unit.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE