

Partial Swing-Out Rack Frame



This 19-in. Partial Swing-Out Rack Frame is used when a smaller, medium-duty swing-out frame is desired. Light-weight rack equipment fits nicely into this 800-mm tall swing-out frame, providing 90 degrees of rotation and increased accessibility.

FEATURES

Side hinge brackets are used to mount the swing frame, allowing free access above and below the swing frame

Used with any height enclosure and hinged on the right or left

Furnished with hinges, two quarter-turn latches and mounting hardware

Complies with ANSI/EIA RS-310-D rack mounting standards:

Swing-Out Rack Frame assemblies are supplied with mounting supports; Swing-Out Rack Frames can also be installed in right, left or both bays of 1200-mm wide frames using center uprights

Swing-out mounting supports mount to inside of frame at any vertical location

Mounting supports and swing-out frame can be located at a variable depth using grid straps; swing is reduced when located at a depth other than front mounted

SPECIFICATIONS

- Thickness: 2.66mm
- Color: Light Gray
- Finish: Powder Coated
- Color Code: RAL 7035

Table 1/1					
Catalog Number	Article Number	Material	Fits Frame Width	Rack Units	Quick Ship
PSF8	99960	Mild Steel	800mm	16U	No
PSF6	99950	Mild Steel	600mm	16U	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE