

RackPower Basic PDU, RB0xxx, 120 VAC, 1-phase

Power Utilities

Modular, compact PDU. Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with NEMA L5 outlets.

FEATURES

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 100 - 120 VAC, 1-phase L-N

Connecting cable 10", with NEMA L5 connector

Nema L5 outlets

1RU aluminum profile

Adjustable Toolless Mounting

SPECIFICATIONS

Table 1/2

| Catalog Number | Product Type | Socket Type | Color | Length | Voltage AC | Depth |
|----------------|--------------|-------------|-------|--------|------------|-------|
| RB0316 | Socket Strip | NEMA 5-20R | Black | 817 mm | 120 V | 53 mm |
| RB0323 | Socket Strip | NEMA 5-20R | Black | 817 mm | 120 V | 53 mm |

Table 2/2

| Catalog Number | Width |
|----------------|-------|
| RB0316 | 52 mm |
| RB0323 | 52 mm |

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE