

# Intelligent PDU, EN1xxx, 230 VAC, 1-PH

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



## FEATURES

Enlogic EN1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 230 VAC, 1-phase

C13, C19 outlets

## SPECIFICATIONS

Table 1/6

| Catalog Number | Product Family | Type            | Product Type | Socket Type                        | Socket Quantity | Color |
|----------------|----------------|-----------------|--------------|------------------------------------|-----------------|-------|
| EN1326         | Enlogic        | Intelligent PDU | Socket Strip | (20) C13, (4) C19                  | 24              | Black |
| EN1325         | Enlogic        | Intelligent PDU | Socket Strip | (20) C13, (4) C19                  | 24              | Black |
| EN1337         | Enlogic        | Intelligent PDU | Socket Strip | (36) C13, (6) C19                  | 42              | Black |
| EN1350         | Enlogic        | Intelligent PDU | Socket Strip | (20) C13/C15, (20) C13/C15/C19/C21 | 40              | Black |

| CatalogNumber | Product Family | Type            | Product Type | Socket Type                                        | SocketQuantity | Color |
|---------------|----------------|-----------------|--------------|----------------------------------------------------|----------------|-------|
| EN1380        | Enlogic        | Intelligent PDU | Socket Strip | (16) Locking C13/C15, (16) Locking C13/C15/C19/C21 | 32             | Black |

Table 2/6

| Catalog Number | Circuit Breaker      | Switched Outlets | Circuit Breaker Quantity | Power Rating | Input Cable Length | Input Cable Location |
|----------------|----------------------|------------------|--------------------------|--------------|--------------------|----------------------|
| EN1326         | No Circuit Breaker   | No               | 0                        | 3.7 kVA      | 3m                 | Top Feed             |
| EN1325         | 16 A, 1-pole, Hy-Mag | No               | 2                        | 7.4 kVA      | 3m                 | Top Feed             |
| EN1337         | 16 A, 1-pole, Hy-Mag | No               | 2                        | 7.4 kVA      | 3m                 | Top Feed             |
| EN1350         | 20 A, 1-pole, Hy-Mag | No               | 2                        | 7.4 kVA      | 3m                 | Top Feed             |
| EN1380         | 20 A, 1-pole, Hy-Mag | No               | 2                        | 7.4 kVA      | 3m                 | Top Feed             |

Table 3/6

| Catalog Number | Input Voltage | Phase | Interrupt Rating | Nominal Voltage | Max Power Input | On/Off Switch Included |
|----------------|---------------|-------|------------------|-----------------|-----------------|------------------------|
| EN1326         | 100 – 240V    | 1 PH  | 5kAIC            | 230V            | 3.3 kVA         | No                     |
| EN1325         | 200 – 240V    | 1 PH  | 5kAIC            | 230V            | 7.44 kVA        | No                     |
| EN1337         | 200 – 240V    | 1 PH  | 5kAIC            | 230V            | 7.44 kVA        | No                     |
| EN1350         | 200 – 240V    | 1 PH  | 5kAIC            | 230V            | 7.44 kVA        | No                     |
| EN1380         | 200 – 240V    | 1 PH  | 5kAIC            | 230V            | 7.44 kVA        | No                     |

Table 4/6

| Catalog Number | Amperage (Derated Amperage) | Output Voltage | Rack Units | Plug Type              | Metering Type | Removable Input Cable |
|----------------|-----------------------------|----------------|------------|------------------------|---------------|-----------------------|
| EN1326         | 16 A                        | 230VAC         | 0U         | IEC 60309 316P6 (IP44) | Input         | Yes                   |

| CatalogNumber | Amperage<br>(Derated<br>Amperage) | Output Voltage | Rack Units | Plug Type                 | Metering Type | Removable<br>Input Cable |
|---------------|-----------------------------------|----------------|------------|---------------------------|---------------|--------------------------|
| EN1325        | 32 A                              | 230VAC         | 0U         | IEC 60309<br>332P6 (IP44) | Input         | No                       |
| EN1337        | 32 A                              | 230VAC         | 0U         | IEC 60309<br>332P6 (IP44) | Input         | No                       |
| EN1350        | 32 A                              | 230VAC         | 0U         | IEC 60309<br>332P6 (IP44) | Input         | No                       |
| EN1380        | 32 A                              | 230VAC         | 0U         | IEC 60309<br>332P6 (IP44) | Input         | No                       |

Table 5/6

| Catalog<br>Number | Material | Finish        | Height | Width | Depth | Weight |
|-------------------|----------|---------------|--------|-------|-------|--------|
| EN1326            | Steel    | Powder Coated | 1490mm | 52mm  | 53mm  | 7.01kg |
| EN1325            | Steel    | Powder Coated | 1490mm | 52mm  | 53mm  | 7.1kg  |
| EN1337            | Steel    | Powder Coated | 1750mm | 52mm  | 53mm  | 8.12kg |
| EN1350            | Steel    | Powder Coated | 1490mm | 56mm  | 55mm  | 8.22kg |
| EN1380            | Steel    | Powder Coated | 1490mm | 56mm  | 55mm  | 8.02kg |

Table 6/6

| Catalog Number | Package Quantity | Quick Ship |
|----------------|------------------|------------|
| EN1326         | 1                | No         |
| EN1325         | 1                | No         |
| EN1337         | 1                | No         |
| EN1350         | 1                | No         |
| EN1380         | 1                | No         |

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE