

APY External Horizontal Wall Bracket



FEATURES

Side mount saddle support for C-Profiles and strut

Complete with fixings


SPECIFICATIONS


Table 1/2							
Catalog Number	Article Number	Material	Finish	Channel Type	Strut Type	Height (H)	
APYSTRUTS6	584840	Stainless Steel 316 (EN 1.4401)			A (41 x 41 mm), C (21 x 41 mm)	50 mm	
APYE23EG	584740	Steel	Electrogalvaniz ed	E2L, E2, E3		40 mm	
APYE4STRUTE G	584751	Steel	Electrogalvaniz ed	E4	A (41 x 41 mm), C (21 x 41 mm)	50 mm	
APYE01EG	584758	Steel	Electrogalvaniz ed	E0L, E0, E1		40 mm	

Table 2/2						
Catalog Number	Article Number	Width (W)	Thickness (T)	A	В	С
APYSTRUTS6	584840	144 mm	5 mm	43 mm	12 mm	19 mm

CatalogNumber	Article Number	Width (W)	Thickness (T)	Α	В	С
APYE23EG	584740	124 mm	5 mm	36 mm	12 mm	19 mm
APYE4STRUTE G	584751	144 mm	5 mm	43 mm	12 mm	19 mm
APYE01EG	584758	124 mm	5 mm	31 mm	12 mm	19 mm

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO

) HOFFMAN

ILSCO SCHROFF

TRACHTE



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.