We connect and protect

19" Front Panel, Plain, 3U, 28 HP, 2.5 mm, Al, RAL 7035

CATALOG NUMBER

30118-331



Front panel without or with SUB-D-, ST type 3- or FDDI cut-out.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

19" Front Panel without Cutout

PRODUCT ATTRIBUTES

Rack Height: 3U
Rack Width: 28HP
Accessory Type: Front panel
Package Quantity: 1
Front Finish: Painted

Rear Finish: Conductive

Color Code: RAL 7035

Depth: 2.5mm

Finish: Powder Coated

Height: 128.4mm

Material: Aluminum

Product Type: Front Panel

Width: 141.9mm

Net Weight: 0.126kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.