

# **Tip-up Foot for Chassis, Plastic**



Flexible and robust Tip-up foot for chassis, with carrying capacity of 25 kg per foot. Suitable for RatiopacPRO/-AIR, PropacPRO, CompacPRO, Comptec and Interscale.

#### **CERTIFICATIONS**



# **FEATURES**

Mounting holes are provided in bottom of case

Load-carrying capacity 25 kg per foot, max case weight: 50 kg

## **SPECIFICATIONS**

**Product Family:** RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac

Product Type: Foot

Type: Foot

Material: Polyamide

Table 1/1			
Catalog Number	Package Quantity	Works With	Quick Ship
20603-001	4	Cases	No
20603-002	4	Cases	No

#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

## **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

# Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

# Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

## Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff

TRACHTE



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF**