

# 610 One-Rod Roller Hanger



## **FEATURES**

Suspend pipe from a single hanger rod where longitudinal movement may occur in the pipe due to expansion or contraction

Conforms with Federal Specification WW-H-171 (Type 44), Manufacturers Standardization Society ANSI®/MSS-SP-58 (Type 43)

## **SPECIFICATIONS**

Material: Steel; Cast Iron

Finish: Hot-Dip Galvanized; Electrogalvanized

Table 1/1						
Catalog Number	Rod Size (RS)	A	В	Static Load		
6100350HD	M12	178 mm	66.68 mm	1735N		
6100400HD	M16	190.5 mm	69.9 mm	2115N		
6101800HD	M24	603.3 mm	266.7 mm	6230N		
6101400HD	M24	479 mm	212.7 mm	5340N		
6101600HD	M24	527.1 mm	241.3 mm	5340N		
6102400HD	M32	787.4 mm	350.8 mm	7115N		


Catalog Number	Rod Size (RS)	A	В	Static Load
6102000HD	M32	660.4 mm	295.3 mm	7115N

## ADDITIONAL PRODUCT DETAILS

Yoke and axle are carbon steel (electrogalvanized) and roll is cast iron (hot-dip galvanized).

Install in accordance with applicable code.

#### **DIAGRAMS**



#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

# Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

ILSCO SCHROFF

**TRACHTE** 

