

# **Cable to Flange Clip**



## **FEATURES**

Provides support for low voltage cables


Requires only a hammer to install

## **SPECIFICATIONS**

Finish: nVent CADDY Armour

Material: Spring Steel

Table 1/1				
<b>Catalog Number</b>	Article Number	Flange Thickness (FT)	Outer Diameter (OD)	A
2H41012A	170460	2 - 3 mm	10.9 - 13 mm	25 mm
2H41214A	170470	2 - 3 mm	12.4 - 16 mm	25 mm
4H241214A	170630	3 - 8 mm	12.4 - 16 mm	25 mm
4H241012A	170480	3 - 8 mm	10.9 - 13 mm	25 mm



### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

## Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 

