

# **Air Terminal Base, Stamped Narrow, Imperial Thread**



#### **CERTIFICATIONS**





# **FEATURES**

For use on narrow flat surfaces

Positive single bolt tension for multi-directional cable clamping

## **SPECIFICATIONS**


Conductor Size, UL: Class 1 - Class 2 (4/0 Max)


Material: Copper

Table 1/2							
Catalog Number	Finish	Thread Size (TS)	Hole Size (HS)	Depth (D)	Height (H)	Width (W)	
LPC304L58	Tinned	5/8" UNC	5 mm	54mm	42 mm	108 mm	
LPC30458		5/8" UNC	5 mm	54mm	42 mm	108 mm	

Table 2/2				
Catalog Number	Unit Weight			
LPC304L58	0.11 kg			
LPC30458	0.11 kg			

## **DIAGRAMS**





#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

MARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

# APAC

Shanghai: + 86 21 2412 1618/19 Sydney:





Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE