

# **Cast U-Bolt Pipe Clamp**



# **CERTIFICATIONS**





## **FEATURES**

Clamp for bonding conductor to handrails, pipes and rebar to lightning protection system


Listed to UL® 96


## **SPECIFICATIONS**

Material: Brass

Conductor Size, UL: Class 1 - Class 2 (4/0 Max);Secondary

Table 1/1						
Catalog Number	Finish	Outer Diameter (OD)	Depth (D)	Height (H)	Width (W)	Unit Weight
LPC570L	Tinned	17.3 - 38.1 mm	45.72mm	76.2 mm	67.82 mm	0.32 kg
LPC570	Bare	17.3 - 38.1 mm	45.72mm	76.2 mm	67.82 mm	0.32 kg





### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

 $^{ extstyle \Delta}$  WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

#### **North America**

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**