

Ground Rod Clamp, Rod to Conductor, Bronze



CERTIFICATIONS











FEATURES

For use with copper-bonded ground rods


Parts that are UL 467 Listed are suitable for direct burial in earth or concrete

SPECIFICATIONS

Table 1/2							
Catalog Number	Article Number	Material	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Conductor Size	Wrench Size	
CP38	158155	Silicon Bronze	3/8"	9.7 mm	#10 Solid - #2 Stranded, 6 mm² Solid - 25 mm² Stranded	9/16"	
C12	158260	Gunmetal	1/2"	12.5 - 12.7 mm	50 mm ² Stranded Max	14 mm	
CP58	158165	Silicon Bronze	1/2" - 5/8"	12.5 - 14.2 mm	#10 Solid - #2 Stranded, 6 mm² Solid - 25 mm² Stranded	3/4"	

CatalogNumber	Article Number	Material	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Conductor Size	Wrench Size
C58	158160	Gunmetal	1/2" - 5/8"	12.5 - 15 mm	70 mm² Stranded Max	14 mm
C19	156900	Gunmetal	5/8" - 3/4"	14.2 - 19 mm	70 mm² Stranded Max	14 mm
C200	156910	Gunmetal	5/8" - 3/4"	14.2 - 20 mm	70 mm² Stranded Max	24 mm
C34	158170	Gunmetal	5/8" - 3/4"	14.2 - 17.2 mm	70 mm² Stranded Max	14 mm
HDC1	158250	Silicon Bronze	1"	25.4 mm	#8 Solid - 4/0 Stranded, 10 mm² Solid - 95 mm² Stranded	13/16"

Table 2/2							
Catalog Number	Article Number	Complies With	Torque (TQ)	Certifications			
CP38	158155		16.90 - 25.4 N·m	UL			
C12	158260		25 N·m Max				
CP58	158165	IEC® EN 62561-1	16.90 - 25.4 N·m	UL, CSA-US, RUS, CSA, cUL			
C58	158160	IEC® EN 62561-1	25 N·m Max				
C19	156900		25 N·m Max				
C200	156910		25 N·m Max				
C34	158170	IEC® EN 62561-1	25 N·m Max				
HDC1	158250		50.8 N·m	UL, cUL			



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

MARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE