

# nVent ERICO Ericontact Insertion Tool, Manual



## FEATURES

Used to insert single and double nVent ERICO Ericontact Rail Contacts

Packaged in a toolbox for safe and convenient handling

Includes two MDRL (715215) Mandrels for 19 mm nVent ERICO Ericontact

## SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Applied Force	Operating Pressure	System
HSKE	715345	57kN	630bar	Hydraulic head with manually-operated hydraulic pump

## ADDITIONAL PRODUCT DETAILS

Kit includes: (2) mandrels for 19 mm nVent ERICO Ericontact rail contact, (1) deburr tool, (1) test gauge, (1) metal case, (1) HSKE pump connected with a high pressure hydraulic hose to the PSKE unit, and (1) manual HSKE.

ERICO ERICONTACT Rail Contact Size	Required Parts	
8 mm	MDRL8ADP (715218) Mandrel Adaptor and MDRL8 (715216) Mandrel	Order separately
13.5 mm	MDRL135ADP (715219) Mandrel Adaptor and MDRL135 (715217) Mandrel	Order separately
19 mm	MDRL (715215) Mandrel	Included
22 mm	PSKECMB (715596) Insertion Head Plate	Order separately

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**