

Plastic Adhesive Base



FEATURES


Mounting base for conductor clips

SPECIFICATIONS

Material: Polypropylene

| Table 1/1 | | | | | |
|----------------|----------------|-------|--------------|------------|-------------|
| Catalog Number | Article Number | Color | Diameter (Ø) | Height (H) | Unit Weight |
| PDCUCABWH | 711345 | White | 63.5 mm | 7.4 mm | 0.01 kg |
| PDCUCABGY | 711343 | Gray | 63.5 mm | 7.4 mm | 0.01 kg |
| PDCUCABBL | 711341 | Black | 63.5 mm | 7.4 mm | 0.01 kg |
| PDCUCABST | 711344 | Stone | 63.5 mm | 7.4 mm | 0.01 kg |
| PDCUCABGN | 711346 | Green | 63.5 mm | 7.4 mm | 0.01 kg |
| PDCUCABBN | 711342 | Brown | 63.5 mm | 7.4 mm | 0.01 kg |





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500

TRACHTE



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF