

Service Entrance Suppressor, 200 kA



FEATURES

200kA 8/20 μ s primary protection rated for service entrance applications

Modular design allows easy replacement of surge modules

Built-in disconnect and fusing eliminates need for external fusing


Transient Discriminating (TD) Technology provides increased service life

SPECIFICATIONS

Catalog Number	SES200120/240
Article Number	700745
Nominal System Voltage (Un)	120/240 V
Distribution System	1Ph 3W+G
Max Continuous Operating Voltage (Uc)	170/340 VAC
Stand-off Voltage	240/480 V
Frequency	50 - 60 Hz
Short Circuit Current Rating (SCCR)	200kA
Nominal Discharge Current (In), Per Mode	80kA 8/20 μ s
Max Discharge Current (Imax), Per Mode	100kA 8/20 μ s
Voltage Protection Rating (VPR)	600 V @ 3 kA L-N 800 V @ 20 kA L-N
Aggregate Surge Rating	200
Impulse Current (Iimp)	20kA 10/350 μ s

Catalog Number	SES200120/240
Max Operating Current	25mA
Protection Modes	All modes protected
Status Indication	5 segment LED bar graph per phase
Technology	TD technology with thermal disconnect
Lead Size	3 - 35 mm ²
Temperature	-10 to 60 °C
Enclosure Material	Polycarbonate
Enclosure Rating	IP 66 NEMA®-4X
Mounting	Wall mount
Depth (D)	190mm
Height (H)	406 mm
Width (W)	305 mm
Unit Weight	8 kg
Certification Details	UL® 1449 Edition 3 Type 1/2, 20 kA Mode
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 3, 100 kA 8/20 µs, 10 kA 10/350 µs

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE