

Stamped U-Bolt Pipe Clamp, 90°



CERTIFICATIONS





FEATURES

Clamp for bonding of pipes, handrails and exhaust stacks to the lightning protection system


Listed to UL® 96


SPECIFICATIONS

Conductor Size, UL: Class 1 - Class 2 (4/0 Max)

Material: Copper;Stainless Steel 304 (EN 1.4301)

Table 1/1					
Catalog Number	Outer Diameter (OD)	Depth (D)	Height (H)	Width (W)	Unit Weight
LPC5962	48.3 - 66.67 mm	50.8mm	92 mm	118.75 mm	0.23 kg
LPC5963	66.8 - 92.2 mm	50.8mm	119.19 mm	139.7 mm	0.35 kg





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY HOFFMAN TRACHTE ERICO ILSCO SCHROFF