

# Threaded Coupler for Copper-Bonded Ground Rod, Threaded



## **CERTIFICATIONS**











# **FEATURES**

High-strength couplings are threaded and chamfered at both ends for easy driving


Corrosion-resistant couplings ensure permanent, low resistance copper-to-copper connections

## **SPECIFICATIONS**

Table 1/2							
Catalog Number	Article Number	Material	Ground Rod Diameter, Nominal	Length (L)	Thread Size (TS)	Unit Weight	
CR58	158040	Bronze	5/8"	61mm	5/8" UNC	0.1 kg	
SC34	158050	Bronze	3/4"	71mm	3/4" UNC	0.17 kg	
CR100		Silicon Bronze	1"	99.1mm	1" UNC	0.35 kg	

Table 2/2							
Catalog Number	Article Number	<b>Complies With</b>	Certifications				
CR58	158040	EN IEC 62561-2	UL, CSA, cUL, CSA-US, RUS				
SC34	158050	IEC® EN 62561-2					
CR100		EN IEC 62561-2	cUL, UL				

### **DIAGRAMS**



## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

MARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

**North America** 

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 APAC

Shanghai: + 86 21 2412 1618/19

+ 00 21 2412 1010/1

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE