


PB Lug for Flat Braids



CERTIFICATIONS



FEATURES

Crimp to FTGB or FRGB braids to create custom flexible connections

Crimped and drilled using BD Crimp and Drill Tool or Crimping Tool for Hydraulic Work Center

RoHS compliant

SPECIFICATIONS

Material: Copper

Finish: Tinned

Table 1/1

Catalog Number	Article Number	Cross Section	Width (W)	Length (L)	Thickness (T)	Unit Weight
PALM-16	557180	16mm ²	16 mm	15mm	1 mm	0 kg
PALM-25	557190	25mm ²	22 mm	25mm	1 mm	0.01 kg
PALM-50	557380	50mm ²	30 mm	30mm	1 mm	0.02 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE