

Tinned Aluminum Earthing and Neutral Busbar



Earthing and Neutral Busbars are used to connect several earthing conductors within a panel and can be used in a variety of different applications such as switchgear and control equipment, electrical equipment, for wind and solar power generation and data centers.

CERTIFICATIONS



FEATURES

Tinned aluminum bar allows for copper or aluminum conductor connections

Use to connect several earthing conductors

Chamfered holes allow for easy connections

Tin plating is corrosion resistant

Rigid bar

Can be fixed using IRS Angle Support Bracket, DMH Metallic Spacer or DH Distance Holder and Spacer

Quick and easy installation

RoHS compliant

SPECIFICATIONS

Material:	Aluminum
Finish:	Tinned
Certification Details:	UL® 467

Catalog Number	EB2AL	EB4AL	EB6AL	EB10AL	EB12AL	EB20AL
----------------	-------	-------	-------	--------	--------	--------

Article Number	568710	568711	568712	568713	568714	568715
Number of Connections	2	4	6	10	12	20
Hole Quantity	3	6	8	12	14	22
Conductor Size, IEC	2.5 - 16 mm ² Stranded	2.5 - 16 mm ² Stranded	2.5 - 16 mm ² Stranded	2.5 - 16 mm ² Stranded	2.5 - 16 mm ² Stranded	2.5 - 16 mm ² Stranded
Conductor Size, UL	#14 - #4 Stranded	#14 - #4 Stranded	#14 - #4 Stranded	#14 - #4 Stranded	#14 - #4 Stranded	#14 - #4 Stranded
Max Current Rating	85A	85A	85A	85A	85A	85A
Height (H)	11.2 mm	11.2 mm	11.2 mm	11.2 mm	11.2 mm	11.2 mm
Width (W)	24.1 mm	47.8 mm	65 mm	96.8 mm	112.5 mm	176 mm
Depth (D)	7.9mm	7.9mm	7.9mm	7.9mm	7.9mm	7.9mm
Unit Weight	0 kg	0.01 kg	0.02 kg	0.03 kg	0.03 kg	0.05 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE