

## Glazed Doors, ADCS



Electrical components can be viewed while the door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

### FEATURES

Description: To replace the standard door, provides a clear view of the components installed inside the enclosure. The lock(s) are interchangeable with all nVent HOFFMAN's standard lock(s)

Material: 1.5 mm AISI 304 stainless steel, 2 mm for enclosures with a height or width of 600 mm or greater and 4 mm clear safety glass

Finish: 400 pre-grained stainless steel

Protection: Complies with IP55, TYPE 12, 13, IK 07.

Pack quantity: 1 door

The glazed door allows the electrical components to be seen while the enclosure's door is closed

The user can monitor the status of the components without the need for opening the enclosure's door maintaining the ingress protection

## SPECIFICATIONS

**Thickness:** 1.5mm  
**Finish:** Brushed  
**Material:** Stainless Steel 304

Table 1/1

Catalog Number	Height	Width	Latch Quantity	Window Size	Enclosure Material	Product Family
ADCS03624	360mm	240mm	1	219 x 83mm	Mild Steel	Wall Mounted
ADCS04030	400mm	300mm	1	259 x 143mm	Mild Steel	Wall Mounted
ADCS04040	400mm	400mm	1	259 x 243mm	Mild Steel	Wall Mounted
ADCS04060	400mm	600mm	1	259 x 443mm	Mild Steel	Wall Mounted
ADCS05040	500mm	400mm	1	359 x 243mm	Mild Steel	Wall Mounted
ADCS05050	500mm	500mm	1	359 x 343mm	Mild Steel	Wall Mounted
ADCS06040	600mm	400mm	2	459 x 243mm	Mild Steel	Wall Mounted
ADCS06060	600mm	600mm	2	459 x 443mm	Mild Steel	Wall Mounted
ADCS06080	600mm	800mm	2	459 x 643mm	Mild Steel	Wall Mounted
ADCS08060	800mm	600mm	2	659 x 443mm	Mild Steel	Wall Mounted
ADCS08080	800mm	800mm	2	659 x 643mm	Mild Steel	Wall Mounted
ADCS10080	1000mm	800mm	1	859 x 643mm	Mild Steel	Wall Mounted
ADCS12080	1200mm	800mm	1	1059 x 643mm	Mild Steel	Wall Mounted
ADCS14080	1400mm	800mm	1	1259 x 643mm	Mild Steel	Wall Mounted

## ADDITIONAL PRODUCT DETAILS

\* 3 point espagnolette locking. Not suitable for AFS.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**