

# Varistar CP IP 20 Cabinet, Glass Front Door, Steel Rear Door

## **Power Utilities**

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

#### **FEATURES**

Type of protection IP 20

With glass front door

Doors with single point locking, side panels with quick release fastener

Static load-carrying capacity 1600 kg

### **SPECIFICATIONS**

Table 1/3						
Catalog Number	Rack Height	Height	Frame Color	Width	Frame Color Code	Cladding Material
10630-038	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Steel
10630-037	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Steel
10630-039	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Steel
10630-040	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Steel

Table 2/3						
Catalog Number	Depth	Cladding Color	Cladding Color Code	Complies With	Frame Material	Product Type

10630-038	800 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Steel	Cabinet
10630-037	600 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Steel	Cabinet
10630-039	600 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Steel	Cabinet
10630-040	600 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Steel	Cabinet

Table 3/3					
Catalog Number	Protection Rating	Static Load			
10630-038	IP20	1600 kgf			
10630-037	IP20	1600 kgf			
10630-039	IP20	1600 kgf			
10630-040	IP20	1600 kgf			

## ADDITIONAL PRODUCT DETAILS

Lever handle can be added to the doors.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

#### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY **ERICO HOFFMAN TRACHTE SCHROFF ILSCO**