

SBS-XX-EV Control Panel for Roof and Gutter De-Icing

nVent RAYCHEM SBS-XX-EV-10 control panel provides an integrated solution for nVent RAYCHEM self-regulating heating cables in roof and gutter de-icing applications. It offers multi-circuits, multi-sensor, and multi-control with integrated electrical protection. Driven by the built-in smart nVent RAYCHEM EMDR-10 control device, it allows the system only to be activated when cold weather and moisture are detected in combination. A 400 VAC (3 phase) supply is required.

FEATURES

Simple and fast connection of multiple circuits, directly into a single panel

High capacity, with 3-12 maximum circuit lengths connected into the panel

Fully integrated system: all connections, circuit protection and safety devices integrated into the panel

Energy saving: through built-in EMDR-10 smart controller, circuits energized only when cold weather and moisture are detected

Reliable, complete system from one manufacturer and specifically designed for roof and gutter de-icing systems

Reliable during long life: 6 year extended product warranty available, maintenance free

SPECIFICATIONS

IP Rating: IP65 **Housing Material:** Steel

Mounting: Wall Mounted

Table 1/2						
Catalog Number	Item Name	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating	Circuit Breaker Quantity, 30 mA	Height
295014-000	SBS-03-EV-10	3	20 A, Type C	32 A	1	600 mm
458484-000	SBS-06-EV-10	6	20 A, Type C	63 A	2	600 mm
282458-000	SBS-12-EV-10	12	20 A, Type C	100 A	4	800 mm

CatalogNumber	Item Name	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating	Circuit Breaker Quantity, 30mA	Height
206336-000	SBS-09-EV-10	9	20 A, Type C	63 A	3	600 mm

Table 2/2						
Catalog Number	Item Name	Width	Depth			
295014-000	SBS-03-EV-10	400 mm	210 mm			
458484-000	SBS-06-EV-10	600 mm	210 mm			
282458-000	SBS-12-EV-10	800 mm	210 mm			
206336-000	SBS-09-EV-10	600 mm	210 mm			

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com Europe, Middle East, Africa Tel +32.16.213.511

Fax +32.16.213.604 thermal.info@nvent.com Asia Pacific

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com Latin America

Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com