

# Collar Screw, Knurled Head Short Version



## **CERTIFICATIONS**



## **FEATURES**

Type:

Collar Screw, Knurled Head Short Version

Screw

## **SPECIFICATIONS**

Works With: Front Panels

Product Type: Screw

Table 1/2									
Catalog Number	Length	Material	Finish	Package Quantity	Thread Size	Depth			
21101-106	11mm	Steel			M2.5				
21101-749	12.3mm	Brass	Nickel Plated	100	M2.5	18.3mm			
21100-268	11mm	Brass	Nickel Plated	100	M2.5				

Table 2/2									
<b>Catalog Number</b>	Height	Width	Torque	Certifications	Quick Ship				
21101-106					No				
21101-749	8mm	8mm	0.3N·m	RoHS	No				
21100-268					No				

#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

## **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

### Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

## Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

## Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF** TRACHTE