nVent | SCHROFF

We connect and protect

AC Fan, 115 VAC, 119 x 119 x 38 mm, 162 m³h

CATALOG NUMBER

20713-244

Axial fan, 119 mm, with AC input. Replacement part for 1 U fan trays.

CERTIFICATIONS

EAC

RoHS COMPLIANT

FEATURES

119 mm DC fan with plug for connection cable

PRODUCT ATTRIBUTES

Product Type: Fan
Works With: 19" Fan Trays
Width: 119mm
Length: 119mm
Height: 38mm
Voltage AC: 115V
Frequency: 50/60 Hz
Airflow @ 50 Hz: 162m³/h
Airflow @ 60 Hz: 192m³/h
Noise Level @ 50 Hz: 37dB(A)
Noise Level @ 60 Hz: 41dB(A)

Power @ 50 Hz: 15W
Power @ 60 Hz: 14W
Max Static Pressure: 73Pa
Ambient Temperature: 70°C
Net Weight: 0.58kg
Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Please order connection cable and protective grille separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.