nVent | SCHROFF

We connect and protect

Socket Strip, SCHUKO, 3-Phase, 9 Sockets

CATALOG NUMBER

60110-219





Modular, compact PDU with SCHUKO outlets and 3-phase connection.

CERTIFICATIONS

EAC

RoHS COMPLIANT

FEATURES

- In accordance with DIN 57620
- Socket strips with SCHUKO sockets, 3-phase
- Connecting cable 2 m, open end with ferrules
- 3 phases, 16 A per phase
- Socket strips can be rotated through all four directions (in 90° increments) during installation
- Installation height 1 U
- Vertical mounting

PRODUCT ATTRIBUTES

- Product Type: Socket Strip
- Socket Type: SCHUKO
- Socket Quantity: 9
- Color: Grey; Black; Red

Switched Outlets: No

Length: 608.5mm

Voltage AC: 230V

Depth: 44mm

Finish: Anodized

Material: Aluminum; Polyamide

Net Weight: 1.65kg

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.