

Intelligent PDU, EN5xxx, 400 VAC, 3-PH

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



FEATURES

Enlogic EN5xxx Intelligent Power Distribution Units monitors input power of the entire PDU and individual outlet monitoring, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

SPECIFICATIONS

Table 1/6

| Catalog Number | Product Family | Type | Product Type | Socket Type | Socket Quantity | Color |
|----------------|----------------|-----------------|--------------|------------------------------------|-----------------|-------|
| EN5402 | Enlogic | Intelligent PDU | Socket Strip | (18) C13, (6) C19 | 24 | Black |
| EN5808 | Enlogic | Intelligent PDU | Socket Strip | (12) C13, (12) C19 | 24 | Black |
| EN5810 | Enlogic | Intelligent PDU | Socket Strip | (24) C13, (12) C19 | 36 | Black |
| EN5812 | Enlogic | Intelligent PDU | Socket Strip | (36) C13, (12) C19 | 48 | Black |
| EN5850 | Enlogic | Intelligent PDU | Socket Strip | (24) C13/C15, (24) C13/C15/C19/C21 | 48 | Black |

Table 2/6

| Catalog Number | Switched Outlets | Circuit Breaker | Power Rating | Circuit Breaker Quantity | Input Cable Location | Input Voltage |
|----------------|------------------|----------------------|--|--------------------------|----------------------|---------------|
| EN5402 | No | No Circuit Breaker | 11.0 kVA | 0 | Top Feed | 380 – 415V |
| EN5808 | No | 16 A, 1-pole, Hy-Mag | 22.0 kVA | 6 | Top Feed | 380 – 415V |
| EN5810 | No | 16 A, 1-pole, Hy-Mag | 22.0 kVA | 6 | Top Feed | 380 – 415V |
| EN5812 | No | 16 A, 1-pole, Hy-Mag | | 6 | Top Feed | 400V |
| EN5850 | No | 20 A, 1-pole, Hy-Mag | 17.3 kVA North America, 22.1 kVA International | 6 | Top Feed | 380 – 415V |

Table 3/6

| Catalog Number | Phase | Interrupt Rating | Nominal Voltage | Max Power Input | On/Off Switch Included | Amperage (Derated Amperage) |
|----------------|----------|------------------|-----------------|-----------------|------------------------|---|
| EN5402 | 3 PH | | 415V | 11.0 kVA | No | 16 A |
| EN5808 | 3 PH | | 415V | 22.0 kVA | No | 32 A |
| EN5810 | 3 PH | | 415V | 22.0 kVA | No | 32 A |
| EN5812 | 3 PH WYE | 5kAIC | | 22.0 kVA | | 32 A |
| EN5850 | 3 PH | | 415V | 17.3 / 22.1 kVA | No | 30 A (24 A) North America, 32 A International |

Table 4/6

| Catalog Number | Output Voltage | Rack Units | Plug Type | Metering Type | Removable Input Cable | Material |
|----------------|----------------|------------|------------------------|---------------|-----------------------|----------|
| EN5402 | 230VAC | 0U | IEC 60309 516P6 (IP44) | Outlet | No | Steel |
| EN5808 | 230VAC | 0U | IEC 60309 532P6 (IP44) | Outlet | Yes | Steel |
| EN5810 | 230VAC | 0U | IEC 60309 532P6 (IP44) | Outlet | No | Steel |

| CatalogNumber | Output Voltage | Rack Units | Plug Type | Metering Type | Removable Input Cable | Material |
|---------------|----------------|------------|---------------------------|---------------|-----------------------|----------|
| EN5812 | 200 – 240VAC | 0U | IEC 60309 532P6 (IP44) | Outlet | No | |
| EN5850 | 208 – 230VAC | 0U | IEC 60309 530P6/532P6 | Outlet | No | Steel |

Table 5/6

| Catalog Number | Finish | Height | Width | Depth | Weight | Package Quantity |
|----------------|---------------|--------|-------|-------|---------|------------------|
| EN5402 | Powder Coated | 1780mm | 52mm | 53mm | 7.82kg | 1 |
| EN5808 | Powder Coated | 1780mm | 52mm | 53mm | | 1 |
| EN5810 | Powder Coated | 1780mm | 85mm | 53mm | 12.23kg | 1 |
| EN5812 | | | | | | 1 |
| EN5850 | Powder Coated | 1780mm | 56mm | 75mm | 11.93kg | 1 |

Table 6/6

| Catalog Number | Input Cable Length | Quick Ship |
|----------------|--------------------|------------|
| EN5402 | 3m | No |
| EN5808 | 3m | No |
| EN5810 | 3m | No |
| EN5812 | | No |
| EN5850 | 1.8m | No |

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE