


# **Novastar Fan Top Cover**



Top covers with fans are compact active cooling units which do not consume rack space. The Novastar fan top cover comes with C14 plug and grounding.

#### **CERTIFICATIONS**



#### **FEATURES**

Connecting cable 0.5 m, IEC C14 plug

St, RAL 7021

Top covers suitable for fan height 25 mm or 38 mm

Incl. grounding and cabling

Fan top cover (33 mm) raised

# **SPECIFICATIONS**

Width: 553mm

**Product Type:** Cabinet/Rack Top Cover

Material: Steel

Table 1/2								
Catalog Number	Depth	Package Quantity	Color	Color Code	Finish	Туре		
27230-081	500mm	1	Black Grey	RAL 7021	Powder Coated	Fan		
27230-082	600mm	1	Black Grey	RAL 7021	Powder Coated	Fan		
27230-083	800mm	1	Black Grey	RAL 7021	Powder Coated	Fan		
27230-085	500mm	1	Black Grey	RAL 7021	Powder Coated	Fan		
27230-086	600mm	1	Black Grey	RAL 7021	Powder Coated	Fan		
27230-087	800mm	1	Black Grey	RAL 7021	Powder Coated	Fan		
27230-094	900mm	1	Black Grey	RAL 7021	Powder Coated	Fan		
27230-095	1000mm	1	Black Grey	RAL 7021	Powder Coated	Fan		
27230-096	900mm	1	Black Grey	RAL 7021	Powder Coated	Fan		
27230-097	1000mm	1	Black Grey	RAL 7021	Powder Coated	Fan		

Table 2/2						
Catalog Number	Certifications	Quick Ship				
27230-081	RoHS, EAC	No				
27230-082	EAC, RoHS	No				
27230-083	RoHS, EAC	No				
27230-085	EAC, RoHS	No				

Catalog Number	Certifications	Quick Ship
27230-086	RoHS, EAC	No
27230-087	EAC, RoHS	No
27230-094	RoHS	No
27230-095	RoHS	No
27230-096	RoHS	No
27230-097	RoHS	No

#### ADDITIONAL PRODUCT DETAILS

Please order lifting eye separately if required.

Please order any additional fans (for increasing cooling capacity) separately.

If required, please order thermostat or speed controller separately.

#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

#### Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

# Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

# Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**