

Varistar CP Base Plate, One-Piece, With Lateral Cable ducting

Varistar CP Base Plate, One-Piece, With Lateral Cable ducting.



FEATURES

Base plate is open at the side; the opening can be covered over with a brush strip

SPECIFICATIONS

Product Type: Cabinet/Rack Base

Material: Steel

| Table 1/2 | | | | | | | | |
|-------------------|-------|--------|---------------------|------------|------------|---------------|--|--|
| Catalog Number | Width | Depth | Package Quantity | Color | Color Code | Finish | | |
| 21630-136 | 600mm | 1200mm | 1 | Black Grey | RAL 7021 | Powder Coated | | |
| 21630-134 | 600mm | 1000mm | 1 | Black Grey | RAL 7021 | Powder Coated | | |
| 21630-139 | 800mm | 1200mm | 1 | Black Grey | RAL 7021 | Powder Coated | | |
| 21630-135 | 600mm | 1100mm | 1 | Black Grey | RAL 7021 | Powder Coated | | |
| 21630-138 | 800mm | 1100mm | 1 | Black Grey | RAL 7021 | Powder Coated | | |
| 21630-137 | 800mm | 1000mm | 1 | Black Grey | RAL 7021 | Powder Coated | | |

| Table 2/2 | | | | | | | |
|----------------|---------------------------|------------|--|--|--|--|--|
| Catalog Number | Туре | Quick Ship | | | | | |
| 21630-136 | Base Plate, Cable Ducting | No | | | | | |
| 21630-134 | Base Plate, Cable Ducting | No | | | | | |
| 21630-139 | Base Plate, Cable Ducting | No | | | | | |
| 21630-135 | Base Plate, Cable Ducting | No | | | | | |
| 21630-138 | Base Plate, Cable Ducting | No | | | | | |
| 21630-137 | Base Plate, Cable Ducting | No | | | | | |

ADDITIONAL PRODUCT DETAILS

Please order brush strip separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

| N | ln | rt | h | Δ | ۱n | n | וב | ri. | ca |
|---|----|----|---|---|----|---|----|-----|----|

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE