

Varistar CP Deco Frame for 800W Cabinet



The deco frame is a perfect fit for the Varistar CP in 800mm width without a front door. It conceals any cabling on the sides of the cabinet, streamlining cable routing and equipment mounting for a more efficient installation process and simultaneously improving the cabinet's appearance.

FEATURES

Conceals cabling beside the 19" panel mount, streamlining cable routing and equipment mounting for a more efficient installation process

Provides easier access to the cabinet's internal components with hinged or removable panels, simplifying maintenance or repairs

Imparts improved functionality, appearance, and durability for Varistar CP cabinets without a door

SPECIFICATIONS

Product Type: Cabinet/Rack Frame

Material: Steel

Table 1/2

Catalog Number	Rack Height	Height	Width	Design Feature	Package Quantity	Color Code
21630-918	38U	1800mm	800mm	Swing frame	1	RAL 7021
21630-919	42U	2000mm	800mm	Swing frame	1	RAL 7021
21630-920	47U	2200mm	800mm	Swing frame	1	RAL 7021
21630-924	38U	1800mm	800mm	19" Slide Mounts	1	RAL 7021
21630-925	42U	2000mm	800mm	19" Slide Mounts	1	RAL 7021

CatalogNumber	Rack Height	Height	Width	Design Feature	Package Quantity	Color Code
21630-926	47U	2200mm	800mm	19" Slide Mounts	1	RAL 7021

Table 2/2

Catalog Number	Finish	Type	Quick Ship
21630-918	Powder Coated	Deco Frame	No
21630-919	Powder Coated	Deco Frame	No
21630-920	Powder Coated	Deco Frame	No
21630-924	Powder Coated	Deco Frame	No
21630-925	Powder Coated	Deco Frame	No
21630-926	Powder Coated	Deco Frame	No

ADDITIONAL PRODUCT DETAILS

The deco frame provides easier access to the cabinet's internal components with hinged or removable panels, simplifying maintenance or repairs. It's an essential addition to any electronics cabinet without a front door, particularly for Automated Test Equipment, providing improved functionality, appearance, and durability.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE